

# WP 830 Raman Spectrometer Series

Keep the signal, lose the fluorescence



## FEATURES AND BENEFITS

- f/1.3 input to capture more light
- Superior optical design based on patented transmissive VPH grating
- >10x faster data sampling rates
- TEC cooling option for best SNR
- SMA fiber coupled, free space, and integrated laser models\*\*
- Compact, robust & configurable
- Excellent thermal stability

We've maximized the efficiency of our spectrometers to give you more sensitivity, better SNR, and faster measurements. Collect more light with our f/1.3 input, keep more light with our high transmission VPH gratings & diffraction-limited optics, and detect more light with scientific-grade detectors. Our build-to-print options for resolution, detector cooling, and sample coupling allow you to configure a spectrometer or integrated system with the exact performance you need.

**Wasatch Photonics offers the expertise & testing to find your optimal Raman solution. Contact us to get started!**

\*\* Integrated laser models are for OEM use only

# WP 830 Raman Spectrometer Series

## STANDARD PRODUCT SPECIFICATIONS & OPTIONS

The configuration options for our build-to-print 830 nm Raman spectrometer and integrated laser systems include slit size (resolution), sample coupling, and detector cooling. We offer ambient, regulated, and TEC cooled detectors, allowing you to balance your required signal to noise (SNR) and temperature stability with cost for the best possible value.

OPTICAL				
DETECTOR COOLING OPTIONS >		Ambient	Regulated	TEC Cooled
Wavenumber Range ( $\lambda_{ex} = 830 \text{ nm}$ )		240 - 1850 $\text{cm}^{-1}$		
Resolution	10 $\mu\text{m}$ slit	4 $\text{cm}^{-1}$		
	25 $\mu\text{m}$ slit	6 $\text{cm}^{-1}$		
	50 $\mu\text{m}$ slit	10 $\text{cm}^{-1}$		
f-number (f/#)		1.3		
Connector (fiber coupled models only)		SMA 905		

DETECTOR & ELECTRONICS				
DETECTOR COOLING OPTIONS >		Ambient	Regulated	TEC Cooled
Hamamatsu Detector		S11510-1006 CCD	S11511-1006 CCD	S10141-1007 CCD
Detector Temperature		ambient	10°C	-15°C
Detector Temperature Stability		-	$\pm 0.2^\circ\text{C}$	$\pm 0.1^\circ\text{C}$
Active Pixels		1024 x 64		1024 x 122
Pixel Size		14 x 14 $\mu\text{m}$		12 x 12 $\mu\text{m}$
Detector Quantum Efficiency: Average / Peak		63% / 76%		46% / 64%
Dynamic Range		50,000		37,500
Signal to Noise Ratio (SNR)		500:1		2400:1
Readout Noise		6 e- RMS		4 e- RMS
Integration Time		3 ms - 60 s		25 ms - 60 s
Maximum Sample Frequency		285 Hz		
Communications		USB 2.0 Type B connector		

MECHANICAL & ENVIRONMENTAL		
	Fiber or Free Space Coupled	Integrated Laser Model (-L)
Size	16.5 x 16.2 x 6.7 cm	22.2 x 16.2 x 6.7 cm
Weight	1.8 kg	2.2 kg
Power Consumption	<500 mA @ 12 V	TBD
Operating Temperature	0°C to 40°C, non-condensing	

LASER (OEM USE ONLY)	
Integrated Laser Model (-L)	
Laser CWL	830 nm
Power	100 mW
Type	Single mode

Custom options available upon request

WP-PS\_WP830-Raman\_13Jan20

